

TB350N008F1

by Acme Electric

Catalog ID: TB350N008F1



ICT .350KVA 240X480-120 F1

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Product Details

General

<p>Application</p>	<p>Acme's CE Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.</p>
--------------------	---

Color	Black
Secondary Voltage	120 V
UPC	047503010921

Dimensions

Dimensions	5.281 in x 4.5 in x 5.2897 in
Height	5.2897 in
Length	5.281 in
Weight	13.6 lb
Width	4.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Logistics

Carton Quantity	1
-----------------	---