

# Industrial Control Transformer .050KVA 240X480-120 F0

By Acme Electric  
Catalog ID: TB50N008F0



By Acme Electric

Catalog ID: TB50N008F0

ICT .050KVA 240X480-120 F0

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

Feedback

## Product Details

### General

---

Application	Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.
-------------	--

---

Color	Black
-------	-------

---

Secondary Voltage	120 V
-------------------	-------

---

UPC	047503010709
-----	--------------

---

kVA	.050
-----	------

---

### **Dimensions**

---

Dimensions	3.32 in x 3 in x 4.0397 in
------------	----------------------------

---

Height	4.0397 in
--------	-----------

---

Length	3.32 in
--------	---------

---

Weight	2.6 lb
--------	--------

---

Width	3 in
-------	------

---

### **Electrical Ratings**

---

Frequency Rating

50/60 Hz

---

Primary Voltage

240 X 480 V

---

### **Certifications and Compliance**

---

Certified Listed

- UL Listed
  - cUL Listed
- 

### **Logistics**

---

Carton Quantity

1

---

Pallet Quantity

168

---

Feedback