



Oh No!
IMAGE COMING SOON

Turnbuckle

by ANDERSON
Catalog ID: TB78JE12

Turnbuckle, 7/8", Jaw-Eye, Forged Steel Take-Up Adj. 12.0 in, UTS 36,000 lb,

Product Details

General

Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Number of Bolt Holes	0
Series	TYPE JE
Strength Rating - Ultimate	36000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359330783
With Jam Nuts	No

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Take Up	12 in
Weight	6.370 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com