



* Representative image

Tee, Bronze Bolted

by ANDERSON
Catalog ID: TCC8100050

Tee, Bronze Bolted, Cable to Cable, 0.46-1.152 Main to 0.325-0.813 Tap.
TEE, BR BOLT .46-1.152 IN .325-.813 IN

Product Details

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Tee, Bolted
UPC	096359331049

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	3.920 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter (Main) - Maximum	1.152 in
Conductor Diameter (Main) - Minimum	0.46 in
Conductor Diameter (Main) Range	0.46 - 1.152
Conductor Diameter (Tap) - Maximum	0.813 in
Conductor Diameter (Tap) - Minimum	0.325 in
Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.46 in
Conductor Diameter Range	0.46 - 1.152
Conductor Type	Copper

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com