



TE2530193S

by Acme Electric
Catalog ID: TE2530193S

Low Voltage Distribution Transformer - Single Phase, 240X480 -
120/240V, 37.5kVA, Non Ventillated

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Non Ventillated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503090671
Winding Material	CU
kVA	37.5

Dimensions

Height	35.47 in
Length	26.9 in
Weight	430 lb
Width	31.9 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R

UL Standard	UL 506
-------------	--------