

Single Gang Device Box, Gangable,  
3 In. Deep, 15 Cu. In., With Raised  
Ground Screw, Recessed Ears, 1/2  
In. Ko (20-Pack), 1004H

By TradeSelect  
Catalog # 1004H



Single Gang Device Box, Gangable, 3 in. Deep, 15 Cu. In., with  
Raised Ground Screw, Recessed Ears, 1/2 in. KO (20-Pack)

Application

These 3" deep device boxes provide more cubic capacity and  
are ideal for larger appliances such as GFCI's, dimmers and  
thermostats or when extra cubic capacity is needed.

General

Bracket Type	No Bracket
Catalog Number	1004H
Drawn or Welded	Welded
Gangable	Yes
Knockouts	4 x 1/2 in
Knockouts - Bottom	2 x 1/2in
Knockouts - End	2 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	Yes
Type	Switch Box, Box
UPC	626463000649
Wiring System	Conduit

Dimensions

Actual Depth	3 in
Raised Ground	Yes
Weight	0.54 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	20
Pallet Quantity	2100

Product Assets

- [3D Product View - 1004H](#)
- [Sales Drawings - 1004H](#)
- [Specifications - 1004H Specification Sheet French](#)
- [Specifications - 1004H Specification Sheet](#)