

Single Gang Device Box, Gangable,  
3 In. Deep, 15 Cu. In., With Raised  
Ground Screw, Side Bracket, Cable  
Pryouts Ends, Nmd90 And Ac90  
(40-Pack), 1004LBU

By TradeSelect  
Catalog # 1004LBU



Single Gang Device Box, Gangable, 3 in. Deep, 15 Cu. In., with  
Raised Ground Screw, Side bracket, Cable Pryouts Ends, NMD90  
and AC90 (40-Pack)

Application

These 3" deep device boxes provide more cubic capacity and  
are ideal for larger appliances such as GFCI's, dimmers and  
thermostats or when extra cubic capacity is needed.

General

Bracket Setback	0.4375
Bracket Type	B, Side Bracket
Catalog Number	1004LBU
Drawn or Welded	Welded
Ends Cable	4
Gangable	Yes
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Switch Box, Box
UPC	626463020661
Wiring System	Non-Metallic Sheathed (NMD)/ Armoured Cable (AC) 14/2 8/3

Dimensions

Actual Depth	3 in
Raised Ground	Yes
Weight	0.59 lb

Conductor Related

Cable Entry	Universal Cable Clamps
-------------	------------------------

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	40
Pallet Quantity	1440

Product Assets

[Specifications - 1004LBU Specification Sheet](#)  
[Specifications - 1004LBU Specification Sheet French](#)