

Utility Box, 1-7/8 In. Deep, 16.5 Cu. In., With Msb Metal Stud Bracket, Raised Ground Screw, 1/2 In. Ko (25-Pack), 1110MSB

By TradeSelect
Catalog # 1110MSB



Utility Box, 1-7/8 in. Deep, 16.5 Cu. In., with MSB Metal Stud Bracket, Raised Ground Screw, 1/2 in. KO (25-Pack)

Application

Utility boxes are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring).

General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	1110MSB
Drawn or Welded	Drawn
Gangable	No
Knockouts	4 x 1/2 in
Knockouts - Bottom	2 x 1/2in
Knockouts - End	2 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Handy Box, Box
UPC	626463040126

Wiring System Conduit

Dimensions

Actual Depth	1.875 in
Raised Ground	Yes
Weight	0.45 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	25
Pallet Quantity	900

Product Assets

[Specifications - 1110MSB Specification Sheet](#)
[Specifications - 1110MSB Specification Sheet French](#)