

Utility Box 1.88 Inches Deep, 14 Cubic Inches, With Knockout, 2020BAR

By TradeSelect
Catalog # 2020BAR



Utility Box 1.88 Inches Deep, 14 Cubic Inches, With Knockout.

Features

- Utility Box 1.88 Inches Deep, 14 Cubic Inches, With Knockout

Application

Utility boxes are used for convenience outlets, switch boxes or small junction boxes. They are popular for exposed work applications (surface mounted wiring).

General

Bracket Type	No Bracket
Catalog Number	2020BAR
Drawn or Welded	Drawn
Gangable	No
Knockouts	10 x 1/2 in
Knockouts - Bottom	2 x 1/2in
Knockouts - End	2 x 1/2in
Knockouts - Side	6 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Handy Box, Box

UPC	626463001509
Wiring System	Conduit

Dimensions

Actual Depth	1.875 in
Raised Ground	Yes
Weight	0.38 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	50
Pallet Quantity	3500

Product Assets

- [3D Product View - 2020](#)
- [Sales Drawings - 2020BAR](#)
- [Specifications - 2020BAR Specification Sheet](#)
- [Specifications - 2020BAR Specification Sheet French](#)