

# Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, 2028FBAR

By TradeSelect  
Catalog # 2028FBAR



Vapor Barrier Ceiling Box, 4" Round, Non-Metallic, Flanged with Vapor Barrier

## Features

- Self-clamping wire entry clamps
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- Front mounted grounding screw with combination straight/Robertson head

## General

Bracket Setback	0.5
Cable Clamps	4
Catalog Number	2028FBAR
Color	Yellow
Material	Thermoplastic Resin
Style	Vapor Barrier
Type	<ul style="list-style-type: none"><li>• Vapor Barrier Box</li><li>• Box</li></ul>
UPC	805035054536
Volume	28.1

## Dimensions

Actual Depth	2.625 in
Depth	2.625 in
Fixture Lbs.	50 lb
Height	7 in
Weight	.265 lb
Width	5.25 in

## Certifications And Compliance

Certified Listed	CSA
------------------	-----

## Logistics

Carton Quantity	40
Pallet Quantity	640

## Product Assets

- [360 Product View - RACO\\_2028FBAR](#)
- [3D Product View - 2028FBAR](#)
- [Brochures - H3672 Banana Boxes](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Nonmetallic Cable Boxes](#)
- [Specifications - 2028FBAR Specification Sheet English](#)
- [Specifications - 2028FBAR Specification Sheet French](#)