

4 In. Square Steel Stud Box, 2-1/8 In. Deep, 30 Cu. In., With Msb Metal Stud Bracket, For 2-3/8 And 3-5/8 In. Stud Size, (20-Pack), 52171MSB

By TradeSelect
Catalog # [52171MSB](#)



4 In. Square Steel Stud Box, 2-1/8 in. Deep, 30 Cu. In., with MSB Metal Stud Bracket, for 2-3/8 and 3-5/8 in. Stud Size, with Concentric and 1/2 in. KO, Raised Ground Screw (20-Pack)

Application

Steel stud boxes are used in Commercial, Residential and Industrial construction.

General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	52171MSB
Drawn or Welded	Drawn
Gangable	No
Knockouts	6 x 1/2 in, 5 x 1/2-3/4 in Combination
Knockouts - Bottom	2 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - End	4 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - Side	1 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	2-Gang
Plaster Ears	No
Type	Square Box, Box

UPC	626463003343
Wiring System	Conduit

Dimensions

Actual Depth	2.125 in
Raised Ground	Yes
Weight	0.61 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	20
Pallet Quantity	700

Product Assets

- [3D Product View - 52171MSB](#)
- [Sales Drawings - 52171MSB](#)
- [Specifications - 52171MSB Specification Sheet French](#)
- [Specifications - 52171MSB Specification Sheet](#)