

4 In. Octagon Box, 1-1/2 In. Deep, 15 Cu. In., With Swing Arm Rework Bracket, Flush Ears, Raised Ground Screw, 1/2 In. Ko, Cable Pryouts, Nmd90 (40-Pack), 54151LDBAR

By TradeSelect
Catalog # [54151LDBAR](#)



4 In. Octagon Box, 1-1/2 in. Deep, 15 Cu. In., with Swing Arm Rework Bracket, Flush Ears, Raised Ground Screw, 1/2 in. KO, Cable Pryouts, NMD90 (40-Pack)

Application

Octagon boxes can be used in the installation of ceiling or wall lighting fixtures. Extension rings provide a means for adding additional cubic capacity.

General

Bracket Setback	0.4375
Bracket Type	D, Swing Arms
Catalog Number	54151LDBAR
Drawn or Welded	Welded
Ends Cable	8
Gangable	No
Knockouts	1 x 1/2 in
Knockouts - Bottom	1 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Type	Octagonal Box, Box
UPC	626463040362
Wiring System	Non-Metallic Sheathed (NMD) 14/2 8/3

Dimensions

Actual Depth	1.5 in
Raised Ground	Yes
Weight	0.56 lb

Conductor Related

Cable Entry	NMD Clamp
-------------	-----------

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	40
Pallet Quantity	1680

Product Assets

- [3D Product View - 54151LD](#)
- [Sales Drawings - 54151LDBAR](#)
- [Specifications - 54151LDBAR Specification Sheet English](#)
- [Specifications - 54151LDBAR Specification Sheet French](#)