

4 In. Steel Stud Octagon Box, 1-1/2 In. Deep, 15 Cu. In., With Msb Metal Stud Bracket, For 2-3/8 And 3-5/8 In. Stud Size, Raised Ground Screw, (25-Pack), 54151MSB

By TradeSelect
Catalog # [54151MSB](#)

4 in. Steel Stud Octagon Box, 1-1/2 in. Deep, 15 Cu. In., with MSB Metal Stud Bracket, for 2-3/8 and 3-5/8 in. Stud Size, Raised Ground Screw, with Concentric and 1/2 in. KO (25-Pack)

Application

Steel stud boxes are used in Commercial, Residential and Industrial construction.

General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	54151MSB
Drawn or Welded	Welded
Gangable	No
Knockouts	2 x 1/2 in, 4 x 1/2-3/4 in Combination
Knockouts - Bottom	2 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - End	2 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Octagonal Box, Box
UPC	626463001998
Wiring System	Non-Metallic Sheathed (NMD) 14/2 8/3

Dimensions

Actual Depth	1.5 in
Raised Ground	Yes
Weight	0.5 lb

Conductor Related

Cable Entry	NMD Clamp
-------------	-----------

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	25
Pallet Quantity	875

Product Assets

- [3D Product View - 54151MSB](#)
- [Sales Drawings - 54151MSB](#)
- [Specifications - 54151MSB Specification Sheet](#)
- [Specifications - 54151MSB Specification Sheet French](#)