

4 In. Steel Stud Octagon Box, 1-1/2 In. Deep, 15 Cu. In., With Msb Metal Stud Bracket, For 2-3/8 And 3-5/8 In. Stud Size, 1/2 In. Ko, (25-Pack), 54151MSBA

By TradeSelect
Catalog # [54151MSBA](#)



4 In. Steel Stud Octagon Box, 1-1/2 in. Deep, 15 Cu. In., with MSB Metal Stud Bracket, for 2-3/8 and 3-5/8 in. Stud Size, 1/2 in. KO, Cable Pryouts Ends, Raised Ground Screw, AC90 (25-Pack)

Application

Steel stud boxes are used in Commercial, Residential and Industrial construction.

General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	54151MSBA
Drawn or Welded	Welded
Ends Cable	8
Gangable	No
Knockouts	1 x 1/2 in
Knockouts - Bottom	1 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Octagonal Box, Box
UPC	626463043455
Wiring System	Armoured Cable (AC) 14/2 8/3

Dimensions

Actual Depth	1.5 in
Raised Ground	Yes
Weight	0.52 lb

Conductor Related

Cable Entry	AC clamp
-------------	----------

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	25
Pallet Quantity	875

Product Assets

- [3D Product View - 54151MSBA](#)
- [Sales Drawings - 54151MSBA](#)
- [Specifications - 54151MSBA Specification Sheet French](#)
- [Specifications - 54151MSBA Specification Sheet English](#)