

4 In. Octagon Box, 2-1/8 In. Deep, 21 Cu. In., With Side Bracket, Raised Ground Screw, 1/2 In. Ko, Cable Pryouts, Nmd90 (50-Pack), 54171LB

By TradeSelect
Catalog # [54171LB](#)



4 In. Octagon Box, 2-1/8 in. Deep, 21 Cu. In., with Side Bracket, Raised Ground Screw, 1/2 in. KO, Cable Pryouts, NMD90 (50-Pack)

Application

Octagon boxes can be used in the installation of ceiling or wall lighting fixtures. Extension rings provide a means for adding additional cubic capacity.

General

Bracket Setback	0.4375
Bracket Type	B, Side Bracket
Catalog Number	54171LB
Drawn or Welded	Drawn
Ends Cable	8
Gangable	No
Knockouts	3 x 1/2 in
Knockouts - Bottom	1 x 1/2in
Knockouts - End	2 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Octagonal Box, Box
UPC	626463003442
Wiring System	Non-Metallic Sheathed (NMD) 14/2 8/3

Dimensions

Actual Depth	2.125 in
Raised Ground	Yes
Weight	0.65 lb

Conductor Related

Cable Entry	NMD Clamp
-------------	-----------

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	50
Pallet Quantity	1400

Product Assets

- [3D Product View - 54171LB](#)
- [Sales Drawings - 54171LB](#)
- [Specifications - 54171LB Specification Sheet](#)
- [Specifications - 54171LB Specification Sheet French](#)