

4" Octagon Box, 2-1/8" Deep, 21 Cu In, 1/2" Ko Nmd90 (10-Pack), 54171LFBAR

By TradeSelect
Catalog # [54171LFBAR](#)



4 In. Octagon Box, 2-1/8 in. Deep, 21 Cu. In., For Ceiling Fan and Fixture 35 Lbs, 1/2 in. KO, Cable Pryouts, Raised Ground Screw, NMD90 (10-Pack)

Application

Octagon Ceiling Fan boxes can be used in the installation of heavy lighting fixtures or ceiling fans.

General

Bracket Type	No Bracket
Catalog Number	54171LFBAR
Ceiling Fan Rated	Yes
Drawn or Welded	Drawn
Ends Cable	8
Gangable	No
Knockouts	3 x 1/2 in
Knockouts - Bottom	1 x 1/2in
Knockouts - End	2 x 1/2in
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Octagonal Box, Box
UPC	626463032428
Wiring System	Non-Metallic Sheathed (NMD) 14/2 8/3

Dimensions

Actual Depth	2.125 in
Raised Ground	Yes
Weight	0.999 lb

Conductor Related

Cable Entry	NMD Clamp
-------------	-----------

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	10
Pallet Quantity	1020

Product Assets

- [3D Product View - 54171LFBAR](#)
- [Sales Drawings - 54171LFBAR](#)
- [Specifications - 54171LFBAR Specification Sheet French](#)
- [Specifications - 54171LFBAR Specification Sheet English](#)