

4 In. Steel Stud Octagon Box, 2-1/8 In. Deep, 21 Cu. In., With Msb Metal Stud Bracket, For 2-3/8 And 3-5/8 In. Stud Size, Raised Ground Screw, (16-Pack), 54171MSB



By TradeSelect
Catalog # [54171MSB](#)

4 In. Steel Stud Octagon Box, 2-1/8 in. Deep, 21 Cu. In., with MSB Metal Stud Bracket, for 2-3/8 and 3-5/8 in. Stud Size, Raised Ground Screw, with Concentric and 1/2 in. KO (16-Pack)

Application

Steel stud boxes are used in Commercial, Residential and Industrial construction.

General

Bracket Setback	0.4375
Bracket Type	MSB, for Steel Stud
Catalog Number	54171MSB
Drawn or Welded	Drawn
Gangable	No
Knockouts	2 x 1/2 in, 4 x 1/2-3/4 in Combination
Knockouts - Bottom	2 x 1/2in, 2 x 1/2-3/4in Combination
Knockouts - End	2 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Octagonal Box, Box
UPC	626463021071

Wiring System	Conduit
Dimensions	
Actual Depth	2.125 in
Raised Ground	Yes
Weight	0.65 lb
Certifications And Compliance	
Certified Listed	CSA
Industry Standard(s)	CSA Certified
Logistics	
Carton Quantity	16
Pallet Quantity	900

Product Assets

- [3D Product View - 54171MSB](#)
- [Sales Drawings - 54171MSB](#)
- [Specifications - 54171MSB Specification Sheet](#)
- [Specifications - 54171MSB Specification Sheet French](#)