



# 1/2 in. EMT Raintight Compression Connector, Uninsulated

By Raco  
Catalog Number [CCSRT050](#)



In wet locations, bond EMT conduit to a box or enclosure use tradeSELECT™ Raintight compression connectors. Offered in two styles, insulated or noninsulated. Designed to comply with current Raintight test requirements and with CEC rule 12-1412.

## Features

- Steel construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Marked with "Wet Location" for easy inspection
- cUL
- Available in trade sizes of 1/2 in. through 4 in.
- Installed knockout seal

## General

UPC 626463044278

## Dimensions

Dimensions	1.004 in x 1.122 in x 1.732 in
Height	1.732 in
Length	1.004 in
Weight	0.12 lb
Width	1.122 in

## Certifications and Compliance

Certification - cULus	cUL Listed
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	250
Minimum Pack Quantity	50
Pallet Quantity	18000

## Product Assets

[Sales Drawings - TRADESELECT RT COMPRESSION CONNECTOR STEEL UNINSULATED CUS](#)  
[Sell Sheets - H3849\\_tradeSELECT\\_Raintight\\_Fittings-Fr](#)  
[Sell Sheets - H3848\\_tradeSELECT\\_Raintight\\_Fittings-Eng](#)

## Related Products

[CCSI050](#)  
[CKS050](#)  
[CCS050](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
TEM\_CA-CCSRT050-SPEC-EN | REV 5/2023