

Masonry Box, 3-1/2 In. Deep, 21 Cu. In., 1-Gang Masonry Box, 2 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (20-Pack), MBD1K

By TradeSelect
Catalog # [MBD1K](#)



Masonry Box, 3-1/2 in. Deep, 21 Cu. In., 1-Gang Masonry Box, 2 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (20-Pack)

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

General

Bracket Type	No Bracket
Catalog Number	MBD1K
Drawn or Welded	Welded
Gangable	No
Knockouts	13 x 1/2-3/4 in Combination, 1 x 1/2-3/4-1 in Combination
Knockouts - Bottom	2 x 1/2-3/4in Combination
Knockouts - End	3 x 1/2-3/4in Combination, 1 x 1/2-3/4-1in Combination
Knockouts - Side	8 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	1-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463003503

Wiring System Conduit

Dimensions

Actual Depth	3.516 in
Raised Ground	Yes
Weight	0.68 lb

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	20
Pallet Quantity	1500

Product Assets

- [3D Product View - MBD1K](#)
- [Sales Drawings - MBD1K](#)
- [Specifications - MBD1K Specification Sheet English](#)
- [Specifications - MBD1K Specification Sheet French](#)