

**Masonry Box, 3-1/2 In. Deep, 63 Cu. In., 3-Gang Masonry Box, 5-10/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (10-Pack), MBD3K**

By TradeSelect  
Catalog # [MBD3K](#)



Masonry Box, 3-1/2 in. Deep, 63 Cu. In., 3-Gang Masonry Box, 5-10/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (10-Pack)

**Application**

Masonry boxes are used for the flush installation of devices in masonry construction.

**General**

Bracket Type	No Bracket
Catalog Number	MBD3K
Drawn or Welded	Welded
Gangable	No
Knockouts	25 x 1/2-3/4 in Combination, 1 x 1/2-3/4-1 in Combination
Knockouts - Bottom	6 x 1/2-3/4in Combination
Knockouts - End	11 x 1/2-3/4in Combination, 1 x 1/2-3/4-1in Combination
Knockouts - Side	8 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	3-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463002698

Wiring System	Conduit
---------------	---------

**Dimensions**

Actual Depth	3.516 in
Raised Ground	Yes
Weight	1.47 lb

**Certifications And Compliance**

Certified Listed	CSA
Industry Standard(s)	CSA Certified

**Logistics**

Carton Quantity	10
Pallet Quantity	560

**Product Assets**

- [3D Product View - MBD3K](#)
- [Sales Drawings - MBD3K](#)
- [Specifications - MBD3K Specification Sheet](#)
- [Specifications - MBD3K Specification Sheet French](#)