

Masonry Box, 3-1/2 In. Deep, 84 Cu. In., 4-Gang Masonry Box, 7-7/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (5-Pack), MBD4K

By TradeSelect
Catalog # [MBD4K](#)



Masonry Box, 3-1/2 in. Deep, 84 Cu. In., 4-Gang Masonry Box, 7-7/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (5-Pack)

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

General

Bracket Type	No Bracket
Catalog Number	MBD4K
Drawn or Welded	Welded
Gangable	No
Knockouts	31 x 1/2-3/4 in Combination, 1 x 1/2-3/4-1 in Combination
Knockouts - Bottom	8 x 1/2-3/4in Combination
Knockouts - End	15 x 1/2-3/4in Combination, 1 x 1/2-3/4-1in Combination
Knockouts - Side	8 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	4-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463002704

Wiring System Conduit

Dimensions

Actual Depth	3.516 in
Raised Ground	Yes
Weight	1.91 lb

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	5
Pallet Quantity	375

Product Assets

- [3D Product View - MBD4K](#)
- [Sales Drawings - MBD4K](#)
- [Specifications - MBD4K Specification Sheet French](#)
- [Specifications - MBD4K Specification Sheet](#)