

Masonry Box, 2-1/2 In. Deep, 42 Cu. In., 3-Gang Masonry Box, 5-10/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (10-Pack), MBS3K

By TradeSelect
Catalog # [MBS3K](#)



Masonry Box, 2-1/2 in. Deep, 42 Cu. In., 3-Gang Masonry Box, 5-10/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (10-Pack)

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

General

Bracket Type	No Bracket
Catalog Number	MBS3K
Drawn or Welded	Welded
Gangable	No
Knockouts	16 x 1/2-3/4 in Combination
Knockouts - Bottom	6 x 1/2-3/4in Combination
Knockouts - End	6 x 1/2-3/4in Combination
Knockouts - Side	4 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	3-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463002858
Wiring System	Conduit

Dimensions

Actual Depth	2.53 in
Raised Ground	Yes
Weight	1.13 lb

Certifications And Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	10
Pallet Quantity	750

Product Assets

- [3D Product View - MBS3K](#)
- [Sales Drawings - MBS3K](#)
- [Specifications - MBS3K Specification Sheet French](#)
- [Specifications - MBS3K Specification Sheet English](#)