

Masonry Box, 2-1/2 In. Deep, 70 Cu. In., 5-Gang Masonry Box, 9-1/4 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (1-Pack), MBS5K

By TradeSelect
Catalog # [MBS5K](#)



Masonry Box, 2-1/2 in. Deep, 70 Cu. In., 5-Gang Masonry Box, 9-1/4 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (1-Pack)

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

General

Bracket Type	No Bracket
Catalog Number	MBS5K
Drawn or Welded	Welded
Gangable	No
Knockouts	24 x 1/2-3/4 in Combination
Knockouts - Bottom	10 x 1/2-3/4in Combination
Knockouts - End	10 x 1/2-3/4in Combination
Knockouts - Side	4 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	5-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463002872
Wiring System	Conduit

Dimensions

Actual Depth	2.53 in
Raised Ground	Yes
Weight	1.84 lb

Certifications And Compliance

Certified Listed	CSA
Industry Standard(s)	CSA Certified

Logistics

Carton Quantity	1
Pallet Quantity	189

Product Assets

- [3D Product View - MBS5K](#)
- [Sales Drawings - MBS5K](#)
- [Specifications - MBS5K Specification Sheet](#)
- [Specifications - MBS5K Specification Sheet French](#)