

**Masonry Box, 2-1/2 In. Deep, 84 Cu. In., 6-Gang Masonry Box, 11-1/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (1-Pack), MBS6K**

By TradeSelect  
Catalog # [MBS6K](#)



Masonry Box, 2-1/2 in. Deep, 84 Cu. In., 6-Gang Masonry Box, 11-1/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (1-Pack)

**Application**

Masonry boxes are used for the flush installation of devices in masonry construction.

**General**

Bracket Type	No Bracket
Catalog Number	MBS6K
Drawn or Welded	Welded
Gangable	No
Knockouts	28 x 1/2-3/4 in Combination
Knockouts - Bottom	12 x 1/2-3/4in Combination
Knockouts - End	12 x 1/2-3/4in Combination
Knockouts - Side	4 x 1/2-3/4in Combination
Material	Steel
Number of Gang(s)	6-Gang
Plaster Ears	No
Type	Masonry Box, Box
UPC	626463002889
Wiring System	Conduit

**Dimensions**

Actual Depth	2.53 in
Raised Ground	Yes
Weight	2.13 lb

**Certifications And Compliance**

Certified Listed	CSA
------------------	-----

**Logistics**

Carton Quantity	1
Pallet Quantity	189

**Product Assets**

- [3D Product View - MBS6K](#)
- [Sales Drawings - MBS6K](#)
- [Specifications - MBS6K Specification Sheet English](#)
- [Specifications - MBS6K Specification Sheet French](#)