



* Representative image

TF220255S

by Acme Electric
Catalog ID: TF220255S

Prop65_Cancer&Reproductive

440Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

Product Details

General

BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	440Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	220Y/127 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503220047
Winding Material	AL
kVA	25

Dimensions

Height	25.5 in
Length	19.4 in
Weight	375 lb
Width	24.4 in

Electrical Ratings

Frequency Rating	50 Hz
Primary Voltage	440D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2

UL Standard	UL 506
-------------	--------