



* Representative image

TF220505S

by Acme Electric
Catalog ID: TF220505S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 440Δ - 220Y/127V, 50kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA2

Product Details

General

BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	440Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	220Y/127 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503090138
Winding Material	AL
kVA	50

Dimensions

Height	29.41 in
Length	22.37 in
Weight	437 lb
Width	28.15 in

Electrical Ratings

Frequency Rating	50 Hz
Primary Voltage	440D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2

UL Standard	UL 1561
-------------	---------