



\* Representative image

## TF279264S

by Acme Electric  
Catalog ID: TF279264S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 190/208/220/240 / 380/416/440/480 - 120/240V, 7.5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

CE Compliant	CE Marked
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503420898
Winding Material	CU
kVA	7.5

### Dimensions

Height	15.19 in
Length	10.84 in
Weight	115 lb
Width	13.5 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/208/220/240 X 380/416/440/480 V

#### Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506