



* Representative image

TF279304S

by Acme Electric
Catalog ID: TF279304S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 190/200/208/220
380V/400/416/440 - 110/220V, 7.5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

CE Compliant	CE Marked
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 200 / 208 / 220 X 380 / 400 / 416 / 440 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	110/220 V
UL Insulation Class	180°C
UPC	047503841822
Winding Material	CU
kVA	7.5

Dimensions

Height	15.19 in
Length	10.84 in
Weight	115 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/200/208/220 X 380/400/416/440 V

Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506