



* Representative image

TP530203S

by Acme Electric
Catalog ID: TP530203S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 -
120/240V, 50kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503201510
Winding Material	CU
kVA	50

Dimensions

Height	25.5 in
Length	19.37 in
Weight	350 lb
Width	24.39 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 2
UL Standard	UL 506