



* Representative image

TP530233S

by Acme Electric
 Catalog ID: TP530233S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 167kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA5

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503001325
Winding Material	CU
kVA	167

Dimensions

Height	45.6 in
Length	35.5 in
Weight	1050 lb
Width	39.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 2
UL Standard	UL 506