



## TP536491S

by Acme Electric  
Catalog ID: TP536491S

Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V,  
37.5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

### Product Details

#### General

BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	220°C
UPC	047503000083
Winding Material	CU
kVA	37.5

#### Dimensions

Height	25.48 in
Length	19.37 in
Weight	257 lb
Width	24.39 in

#### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208 V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 506

