



TP536513S

by Acme Electric
Catalog ID: TP536513S

Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V,
75kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA3

Product Details

General

Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	220°C
UPC	047503089903
Winding Material	CU
kVA	75

Dimensions

Height	35.4 in
Length	26.88 in
Weight	420 lb
Width	31.9 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 506

