

UltraVac 20kV, 125kV BIL, 200A Solid Dielectric Vacuum Switch, 33"

By Trinetics
Catalog # [33247402](#)

24kV, 150kV BIL, 200A vacuum switch in solid dielectric insulation, with manual handle, 120V solenoid operator, 5-pin receptacle, NEMA type pole mounting hanger, and (2) wildlife guards



*Representative Image

Features

- Our most flexible line of switches, UltraVac vacuum capacitor switches can accommodate a wide variety of switching applications while simultaneously offering a unique combination of longevity.
- Such as maintenance-free operation, durability, reliability, high dielectric strength, easy installation and performance that surpasses ANSI standards.
- UltraVac switches are designed for 110kV, 125kV and 150kV BIL applications.
- Best-in-class C2 restrike rating.
- 5-pin auxiliary receptacle included standard, but optional auxiliary contacts are available.

General

Interruption Type	Cycloaliphatic Epoxy
Operating Mechanism	Motor
Switch Type	Vacuum in solid dielectric
Type	UltraVac
UPC	096359624943

Electrical Ratings

Creep and Leakage Distance	33"
Current Rating	200 A
Operating Voltage	120 VAC
Phase	Single Phase

Product Assets