

**2 Pole, 100 Amp Relay**

By Trinetics  
Catalog # [MR-DRC](#)

2-pole, 240/480V, Norm Open; Form A air contact, 100A; Load protection: Fuse; Line/load circuit arresters: Spark Gap; Coil voltage: 120V; Control circuit source: Line/Internal Transformer; HOA: Internal/External Wired; in a weather proof case.

**Features**

The MR Series is the foundation of the Trinetics product line of multiple relay lighting controls. MR relays feature a time-proven electromagnetic design that provides high compression, low audible noise and minimum eddy current heating. For customers in need of heavy duty construction and long-term performance, the MR Series is built for years of trouble-free service in the most challenging environments.

**General**

Catalog Number	MR-DRC
Circuit Protection	Fuse
Contact	Air
Contact Configuration	N.O.



Material	Cast Aluminum
Number Of Poles	2
Size	17-1/4 x 11-7/16 x 8-1/4
UPC	096359633297

**Electrical Ratings**

Amperage Rating	100 A
Coil Voltage	120V
Voltage Rating	240/480 V

**Product Assets**

[Sales Drawings - Relay Assembly MR-DRC Spec 6900 \(33202401\)](#)  
[Specifications - MRDRC](#)