

1 Pole, 60 Amp Relay

By Trinetics
Catalog # [MR-HG](#)


1-pole, 480V, Norm Open; Form A air contact, 60A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Photocell provision: Mounted Receptacle; Control circuit arrester: Spark Gap; in a weather proof case.

Features

The MR Series is the foundation of the Trinetics product line of multiple relay lighting controls. MR relays feature a time-proven electromagnetic design that provides high compression, low audible noise and minimum eddy current heating. For customers in need of heavy duty construction and long-term performance, the MR Series is built for years of trouble-free service in the most challenging environments.

General

Catalog Number	MR-HG
Circuit Protection	Fuse
Contact	Air



Contact Configuration	N.O.
Material	Cast Aluminum
Number Of Poles	1
Size	17-1/4 x 11-7/16 x 8-1/4
UPC	096359705697

Electrical Ratings

Amperage Rating	60 A
Coil Voltage	120V
Voltage Rating	480 V

Product Assets

[Sales Drawings - Relay Assembly MR-HG Spec 6398 \(31195503\)](#)
[Specifications - MRHG](#)