

HUBBELL Power Systems

2 Pole, 30 Amp Relay

By Trinetics
Catalog # [MR-WCLX](#)

2-pole, 120/240V, Norm Open; Form A air contact, 30A; Load protection: Circuit Breaker; Coil voltage: 120V; Control circuit source: Line; HOA: Internal ; Control circuit arrester: Spark Gap; in a weather proof case. (Special)

Features

The MR Series is the foundation of the Trinetics product line of multiple relay lighting controls. MR relays feature a time-proven electromagnetic design that provides high compression, low audible noise and minimum eddy current heating. For customers in need of heavy duty construction and long-term performance, the MR Series is built for years of trouble-free service in the most challenging environments.

General

Catalog Number	MR-WCLX
Circuit Protection	C.B.
Contact	Air



Contact Configuration	N.O.
Material	Cast Aluminum
Number Of Poles	2
Size	14 3/16 x 9 x 5 1/8

Electrical Ratings

Amperage Rating	30 A
Coil Voltage	120V
Voltage Rating	120/240 V

Product Assets

[Sales Drawings - Relay Assembly MR-WCLX Spec None \(33033000X003\)](#)
[Specifications - MRWCLX](#)