

SmartClose 27kV, 125kV BIL, 400A Synchronous Vacuum Switch, 18"

By Trinetics

Catalog # [SMC27-125E1D2ME6XX](#)

27kV, 125kV BIL, 400A 3ph tank capacitor switch with 3-120V solenoid operators for optional independent pole operation, 3 manual open/close handles, 6 integral voltage sensors, substation frame compatible mounting flange, 5-pin receptacle for control cable, and fiber optic compartment with 2 AVAGO snap-on bulkhead connectors. Includes wildlife covers

General

Catalog Number	SMC27-125E1D2ME6XX
Interruption Type	Cycloaliphatic Epoxy
Operating Mechanism	Solenoid
Switch Type	Vacuum synchronous
Type	SmartClose (3-phase switch)

Dimensions

Height	0 in
Length	0 in



Width 0 in

Electrical Ratings

Creep and Leakage Distance	18"
Current Rating	400 A
Operating Voltage	120 VAC
Phase	Three Phase

Product Assets

[Specifications - SMC27-125E1D2ME6XX](#)