



# TSC400-400K

by CMC  
Catalog ID: TSC400-400K

Compression Cable Splice with 600 Volt EPDM Rubber Cover



- Splice kits include a ready-to-use compression sleeve splice, a type TSC splice cover of EPDM rubber, a pack of silicon, grease, and an instruction sheet.
- Aluminum sleeves are intended for splicing aluminum to aluminum or aluminum to copper wires
- Can be used for completely submersed, direct burial, cable tray, or other 600-volt applications

## Product Details

### General

Die Size	<ul style="list-style-type: none"><li>• Kearney 1-1/8-1, 1-1/8-2</li><li>• Burndy 316, 655, 705 or 13A</li></ul>
Material	Aluminum
Type	TSC-K

### Dimensions

Length	12.78 in
--------	----------

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor - ACSR Cmpt Size A	500
Conductor - AL Str Size A	336;400
Conductor - Copper Str Size A	336;400



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

