

tradeSELECT® BANANA BOX™

Non-metallic Box, 1-Gang, 18 Cu. In., with side bracket

By tradeSELECT
Catalogue # 2001R

Non-Metallic Boxes, Device Boxes, For use with non-metallic sheathed cable, 18 Cu. In., 1-gang with side Bracket, 1/2 in. setback, 4 Cable Clamp, Molded from high-strength plastic resin. (50-Pack)



Feature

- Preset tabs at 1/2" for fast positioning
- Breakable tabs, perfect for double drywall installation.
- Engravings at 5/8", 1", 1-1/8" and 1-1/4" ensure box placement in accurate and consistent depths, while reducing the installation time
- Superior cubic capacity - Additional volume makes termination easier and is excellent for deeper body devices
- Oversized nailing / screw bracket for better reach to mount on stud or joint
- High hammer impact resistant when nailing
- Lightweight
- Bright yellow color helps to locate wires in low light levels

Application

Accommodates wiring devices such as switches and receptacles

General

Bracket Setback	0.50"
Colour	Yellow
Fire Resistance	Yes
Material	Thermoplastic Resin
Number of Gang(s)	1-Gang
Type	Non-Metallic Box
UPC	805035000038
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Cubic Capacity	18 Cu. In (295mL)
Depth	2.82 in
Height	3.73 in
Weight	0.196 lb
Width	2.27 in

Certifications and Compliance

Industry Standard(s)	cCSAus Certified
CSA Cable Range NMD-90	14/2, 14/3, 12/3, 12/2 or 10/2
UL CABLE RANGE NM-B	14/2, 14/3, 12/3, 12/2 or 10/2

Logistics

Carton Quantity	50
Pallet Quantity	2700

Product Assets

3D Product View



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved. Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Inc. All other trademarks are the property of their respective owners.

Hubbell Canada | 870 Brock Rd S, Pickering, ON L1W 1Z8
hubbell.ca | 800-465-7051

tradeSELECT-2001R-Spec-Sheet-08-2024-CanEN-V2