



USM350-4I

by CMC

Catalog ID: USM350-4I

Space-saver stud-mount transformer connectors which allows left or right -hand mounting, Dual-Rated for Aluminum or Copper Conductors

- Designed to reduce cantilever stress on the bushing by 50% and increase available safe space
- Clear plated for low-contact resistance
- Allows left or right-hand installation
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Offers fast, economical, reusable, dependable connections for right or left-hand installations
- Supplied with aluminum radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- 105°C Rated clear plastisol cover available
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench
- For use on both 5/8" and 1" studs in screw-on and quick-disconnect models

Product Details

General

Series	USSM
Type	USSM/USM

Dimensions

Dimensions	4.66 in x 1.25 in x 2.88 in
Height	2.88 in
Length	4.66 in
Width	1.25 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: jrex@cmclugs.com

