

USM350-6

by CMC

Catalog ID: USM350-6



Space-saver stud-mount transformer connectors allows left or right-hand mounting, Screw-On, Dual rated connectors for Aluminum or Copper conductors, CO-OX Oxide inhibitor is omitted

- Designed to reduce cantilever stress on the bushing by 50% and increase available safe space.
- Clear plated for low-contact resistance.
- Allows left or right-hand installation
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Offers fast, economical, reusable, dependable connections for right or left-hand installations.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- 105°C Rated clear plastisol cover available.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.
- For use on both 5/8" and 1" studs in screw-on and quick-disconnect models.

Product Details

General

Material	Aluminum Alloy, 6061-T6
----------	-------------------------

Dimensions

Height	2.88 in
Length	7.04 in
Width	1.25 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	6



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

