

# USSM350-4

by CMC

Catalog ID: USSM350-4



Space-saver stud-mount transformer connectors allows left or right-hand mounting, Slip-On, Dual rated connectors for Aluminum or Copper conductors, CO-OX Oxide inhibitor is omitted

- Designed to reduce cantilever stress on the bushing by 50% and increase available safe space.
- Clear plated for low-contact resistance.
- Allows left or right-hand installation
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Offers fast, economical, reusable, dependable connections for right or left-hand installations.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- 105°C Rated clear plastisol cover available.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.
- For use on both 5/8" and 1" studs in screw-on and quick-disconnect models.

## Product Details

### General

|          |                         |
|----------|-------------------------|
| Material | Aluminum Alloy, 6061-T6 |
| UPC      | 192663075034            |

### Dimensions

|        |         |
|--------|---------|
| Height | 2.88 in |
| Length | 4.66 in |
| Width  | 1.25 in |

### Electrical Ratings

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

|                      |                     |
|----------------------|---------------------|
| Conductor Range      | 350 Kcmil - #12 AWG |
| Number Of Conductors | 4                   |



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex@cmclugs.com](mailto:jrex@cmclugs.com)

