



VC-2

by CMC
Catalog ID: VC-2

Bronze Distribution Connector

- Complies with all ANSI specifications and provides a vibration-proof connection
- One-piece design eliminates loose parts and danger of cross threading. “V” grooves assure perfect alignment of conductors and provide self-cleaning during installation
- The long thread engagement provides strength, ease of covering and protection from the elements for removal and reuse
- High pressure between conductors at low torque assures a strong mechanical joint and high electrically conductive contacts
- Easy installation with gloves or “hot sticks”
- Overlapping wide range and complete selection for all conductors, permits smaller inventory
- The broad base permits assembly on structures or pads as a ground connector for cable flat applications.

Product Details

General

UPC	192663139651
-----	--------------

Dimensions

Width	0.88 in
-------	---------

Conductor Related

Conductor Range	#6 AWG to #2 AWG
-----------------	------------------

Logistics

Pallet Quantity	12000
-----------------	-------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

