



VC-40

by CMC
Catalog ID: VC-40

Bronze Distribution Connector

- Complies with all ANSI specifications and provides a vibration-proof connection
- One-piece design eliminates loose parts and danger of cross threading. "V" grooves assure perfect alignment of conductors and provide self-cleaning during installation
- The long thread engagement provides strength, ease of covering and protection from the elements for removal and reuse
- High pressure between conductors at low torque assures a strong mechanical joint and high electrically conductive contacts
- Easy installation with gloves or "hot sticks"
- Overlapping wide range and complete selection for all conductors, permits smaller inventory
- The broad base permits assembly on structures or pads as a ground connector for cable flat applications.

Product Details

General

UPC	192663121748
-----	--------------

Dimensions

Width	0.49 in
-------	---------

Conductor Related

Conductor Range	#1 Sol. - #4/0 Sol.
-----------------	---------------------