



Oh No!
IMAGE COMING SOON

In-line Test Gauge

by ANDERSON
Catalog ID: VCLPG

In-line test gage for remote tools.

- Operates in-line during crimp cycles, large easy to read gage is shatter-proof.
- 3/8" male coupler on one end, 3/8" female on other, plastic carrying case.
- For Remote Power Supplies.

Product Details

General

Style	Test Gage
UPC	096359336877

Dimensions

Weight	5.684 lb
--------	----------

Conductor Related

Crimping Size - Maximum	0 in
Crimping Size - Minimum	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com