



* Representative image

Terminal, Bronze Bolted

by ANDERSON
Catalog ID: VL3D92DH

Terminal, Bronze Bolted, Three Cables to Flat, Eyebolt style, cable range 1.152-1.412, Centerformed pad: 4 hole, 4 in. TERMINAL, BR EB (3) 1.152-1.412 IN-D PAD

- Cable entrance only from end of terminal, 90° pad orientation available

Product Details

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Eyebolts	3
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Terminal / Lug, Bolted
UPC	096359353058

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	11.760 lb
Width - Pad	4 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.412 in
Conductor Diameter - Minimum	1.152 in
Conductor Diameter Range	1.152 - 1.412
Conductor Type	Copper

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com