



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

## W2A4C9DP47L

by Wiegmann  
 Collection Name: Guardian  
 Catalog ID: W2A4C9DP47L

Nema 4 Guardian Series Air Conditioner, 47x17x10, 9,000 BTU/H, 230 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

### Product Details

#### General

Color	Gray
Series	DP 47 Series (9,000 BTU/H)
Type	Air Conditioner
UPC	786725871933

#### Dimensions

Actual Depth	10 in
Actual Height	47 in
Actual Width	17 in
Weight	135 lb

#### Electrical Ratings

Hertz Input	60
Voltage Rating	230 V

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> <li>• UL</li> <li>• cUL</li> </ul>
Nema Rating	4