



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

W2NA4C3DP24L

by Wiegmann

Collection Name: Guardian

Catalog ID: W2NA4C3DP24L

Nema 4 Guardian Series Air Conditioner, 24x12x10, 3,000 BTU/H, 230 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

Product Details

General

| | |
|--------|----------------------------|
| Color | Gray |
| Series | DP 24 Series (3,000 BTU/H) |
| Type | Air Conditioner |
| UPC | 786725888139 |

Dimensions

| | |
|---------------|-------|
| Actual Depth | 10 in |
| Actual Height | 24 in |
| Actual Width | 12 in |
| Weight | 61 lb |

Electrical Ratings

| | |
|-----------------|-------|
| Amperage Rating | 3 |
| Hertz Input | 60 |
| Voltage Rating | 230 V |

Certifications and Compliance

| | |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none"> • UL • cUL |
| Nema Rating | 4 |