



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

W2NA4C5DP33L

by Wiegmann

Collection Name: Guardian

Catalog ID: W2NA4C5DP33L

Nema 4 Guardian Series Air Conditioner, 33x17x11, 5,000 BTU/H, 230 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

Product Details

General

Color	Gray
Series	DP 33 Series (5,000 BTU/H)
Type	Air Conditioner
UPC	786725889228

Dimensions

Actual Depth	11 in
Actual Height	33 in
Actual Width	17 in
Weight	95 lb

Electrical Ratings

Hertz Input	60
Voltage Rating	230 V

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • cUL
Nema Rating	4