



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

## W2NA6C18DP53L

by Wiegmann

Collection Name: Guardian

Catalog ID: W2NA6C18DP53L

Nema 4 Guardian Series Air Conditioner, 53x22x13, 18,000 BTU/H, 230 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

### Product Details

#### General

|        |                             |
|--------|-----------------------------|
| Color  | Gray                        |
| Series | DP 53 Series (18,000 BTU/H) |
| Type   | Air Conditioner             |
| UPC    | 786725888221                |

#### Dimensions

|               |        |
|---------------|--------|
| Actual Depth  | 13 in  |
| Actual Height | 53 in  |
| Actual Width  | 22 in  |
| Weight        | 224 lb |

#### Electrical Ratings

|                |       |
|----------------|-------|
| Hertz Input    | 60    |
| Voltage Rating | 230 V |

#### Certifications and Compliance

|                  |   |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none"> <li>• UL</li> <li>• cUL</li> </ul> |
| Nema Rating      | 4   |